



DRAWING NO	TM523-AN10		
PART NAME	Console Set		
PART NO	1000233833		
APPROVE	KYLE	DATE	092812



Part NO	Description
1000233833	Console Set;ES;ENG;T3x

DRAWING NO	TM522-AT11		
PART NAME	Switch Set; Emergency		
PART NO	1000300535	REV	B
APPROVE	KENNY	DATE	2012.07.16



Bubble #	Part Number	Description
10	1000233833	Console Cover Set;-;up;ES;1US;T-3X-05-C;
17	1000231006	Safety Key Set;T-1x-03-C;
9	Order kit 10	Console Set;ES;1US;H001S001;T-3x-04-C;
AN10	0000086724	Cover;Console Display;TV Rack;Printing;T
AN24	1000229245	Repair Cover;Console;-;ABS/PA746;SL/GY/8
AN4	1000352475	Switch Clip Set;Safety;;Red;
AN4	1000231246	Safety Switch Set;BL Rope;TM501-1US;TM50
AN9	Part of Kit 17	Safety Key Cover-Extrawork,up,Print,-,TM
N03	Part of Kit 9 or 10	Console Faceplate;PC 510;Gray/80435;T-3x
N06	1000229248	Documentation;Manipulate Overlay;Down;T-
N07	1000229383	Membrane Keypad,Membrane,1,PC;0.5t,T-1x-
N09	0000088791	TV Earphone Wire Cover;ABS/PA746;80435
N10	1000231624	Console Cover,back,ABS 746,SL/GY,80547,T
N11	1000231625	Console Cover,Kettle Rack,left,ABS 746,S
N12	1000231626	Console Cover,Kettle Rack,right,ABS 746,
N16	1000226522	Extrawork;USB Cover;Printing;TM521;
N20	1000229301	Documentation;Manipulate Overlay;UP;Engl
N26	1000229104	Keypad function;21keys;T-3x-04-C;
N27	1000226524	Torsional Spring;-;USB;SUS304;TM521
N28	1000226525	Fixing Plate;USB;SECC;1.0t;T-7xi-C;
N29	1000303128	Foam;-;48x5x3.0t;Black;-;TM524
N30	Part of Kit 17	Fix Plate;Emergency;SPHC;1.6t;BED;TM501;
N34	0000085362	Screw;SH;M8X1.25PX20L;;HS;;BAN;;
N37	008864-A	Screw;Special;Round;2.9x1.06Px7L(Hi-Lo)
N38	0000095985	Washer;Flat;8.2x19.0x2.0T;BED;
N39	1000228688	SCREW;BH;M5X0.8PX12L;PH;BAN;
N44	Part of Kit 17	Cover;Safety Key;down;ABS 746;137C
N47	1000228682	Control Board;C-SAFE;H001;NA;TM519
N49	020016-AB	Screw;Phillip;BH;Stainess;M5x0.8Px30L;
N50	1000231688	SCREW;BH;?p5x1.6Px35L(HI-LO);PH;BZN;
N54	0000086912	Translator Board;Console;H002;T1x;
N57	1000229263	TV Signal;1700;(FM-0086-NBG7)x2
N59	1000229265	COMM Wire Digital;2100(MOLEX,50-70-9408x
N69	1000229073	Wire;Keypad;300(3M1DC 7920-B500x2);T-1x-

Bubble #	Part Number	Description
N70	1000231005	WIRE;H/P;-;-;200(2510A-03 XAP-03);T-1X
N71	1000229262	Grip Sensor;300+550mm;(TKP,2510A-06+TKP,
N72	010515-00	Copper Pillar;M3x12L
N81	0000088743	Screw;TRH;M3x.5Px6L;MT;PH;CST;ZNC;F-T
N82	0000091827	Filter Ground Wire;300L;KST FDFNYD2-250
N83	004627-00	Screw;Phillip;BH;Tapped;5x12L
N85	1000231078	SCREW;BH;?X5X1.6PX12L(HI-LO);PH;BZN;
N87	1000229267	Wire;GND;Pulse Board;150(KST,MDFNYD2-250
N90	1000229074	Heart rate receiver,RF HR,Salutron 8600,
N92	1000229264	Wire;TV Power;1700(H6630P1-04+H6630R1-04
N93	1000229105	Wire;C-SAFE+TV;600(TKP,H20J2-15)x2;
N95	020050-Z	Screw;BH;Sunk;M6X1X20;Zinc
Not Shown	0000089228	Earphones Cover;Printing;T1xe- D/C,
Not Shown	1000231589	SCREW;BH;M3X0.5PX6L;CT;PH;SST;BAN;
Not Shown	1000229115	Wire;Ear Phone Board;150(TKP,H6630P1-04+
Not Shown	0000089835	Washer;Ribbed lock;8.5x12.8x0.8tx1.3h;
Not Shown	1000231014	WIRE;NETWORK SIGNAL;UP;500(AMP,56953
Not Shown	004356-AB	Screw;Phillip;BH;M4x0.7Px12L;BED;
Not Shown	065248-A	TV Coax Adaptor;Female;F-A028-NBX7-C
Not Shown	1000231009	OVERLAY SET;TV;T-1X-04-C;-;
Not Shown	1000232989	E-PORT PWR;-;-;800mm;(AMP,5-554739-3)x2
Not Shown	004475-00	SCREW;SH;M8X1.25PX15L;;HS;;BZN;;
Not Shown	0000086157	Signa Wire;TV;U;500(FM-0086-NBG7)x2
Not Shown	1000232990	LCD CTRL;-;-;500mm;(AMP,5-554739-3)x2
Not Shown	1000231008	WIRE;TV POWER;UP;-;-;500(H6630R1-04 DC 2
P24	004370-00	Screw;Phillip;BH;M5x0.8Px10L;;Zn-BL
P25	001682-00	Clip;Tie Strap Hold Down;HC-0L;P
P26	001597-A	GROMMET;NYLON;WHT
P29	0000093219	Jacket;PVC;A5X-03-F;US;EP79
P30	1000232715	Network Signal,1700,TKP,H6630P1-08 TKP,H
T02	0000084630	Safety Switch;R13-69;TM501;
T03	1000231004	WIRE;CONNECT;400(250X2 6630R1);T-1x-03-C
T09	004614-00	Screw;BH;3X10L;SM;PH;;BAN;;POT
T11	0000093244	Screw;Phillip;BH;Tapped;4x8L;Zn-BL;

Bubble #	Part Number	Description
W01	1000228614	Control Board;Console;;S003;T-3X-04-C;TM - D/C,
W04	1000213752	Control Board;USB;H001;U10CA1;
W18	1000210330	Wire;Connect;USB;250(JST,XAP-06V-1)x2;